

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282033

Luminaire Tested: P3AS05R55B2750DE010 E3D1WMH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3D1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 505.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282033

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282033

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	81	81	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	76	76	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	72	72	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	68	68	67
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	65	65	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	61	61	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	58	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146436
5°	141250
10°	146312
15°	144246
20°	133502
25°	107958
30°	64693
35°	21924
40°	6040
45°	2667
50°	785
55°	153
60°	88
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2667 cd/sqm

TEST NUMBER: P1282033

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.1	12.3
10°-20°	176.9	35.0
20°-30°	196.6	38.9
30°-40°	61.2	12.1
40°-50°	7.3	1.5
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.6	86.3
0°-40°	496.9	98.4
0°-60°	504.8	100.0
0°-90°	505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	505.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	642	62
15°	635	177
25°	446	197
35°	82	61
45°	9	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1282033

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	667.8
1°	665.3
2°	658.8
3°	650.8
4°	643.5
5°	641.7
6°	643.7
7°	647.7
8°	652.3
9°	655.9
10°	657.1
11°	656.3
12°	653.3
13°	648.5
14°	642.9
15°	635.4
16°	626.8
17°	615.8
18°	603.6
19°	588.8
20°	572.1
21°	553.1
22°	530.7
23°	505.9
24°	477.5
25°	446.2
26°	411.9
27°	375.5
28°	336.5
29°	296.4
30°	255.5
31°	214.5
32°	174.4
32.5°	156.6
33°	138.1
34°	106.9
35°	81.9
36°	62.4
37°	46.2
37.5°	39.5
38°	34.3
39°	26.1
40°	21.1
42.5°	13.4
45°	8.6



TEST NUMBER: P1282033

CATALOG NUMBER: P3AS05R55B2750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.2
50°	2.3
52.5°	0.8
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)