

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1280951

Luminaire Tested: P3AS05R15B2750DE010 E3DLP1MW\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1280951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R15B2750DE010 E3DLP1MW\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 80CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 262.0 lumens  
Efficiency: N/A  
Efficacy: 44.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1280951

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1MW\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1280951

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 93  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 87  | 79  | 73  | 69  | 77  | 72  | 69  |  | 76  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 65  | 83  | 74  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  |
| 9   | 77  | 68  | 62  | 58  | 76  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 57  |  | 64  |
| 10  | 74  | 64  | 59  | 55  | 73  | 64  | 59  | 55  | 63  | 58  | 55  |  | 62  | 58  | 55  |  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 112973 |
| 5°  | 104424 |
| 10° | 83365  |
| 15° | 62974  |
| 20° | 47954  |
| 25° | 36534  |
| 30° | 26181  |
| 35° | 17079  |
| 40° | 10477  |
| 45° | 6326   |
| 50° | 4196   |
| 55° | 3250   |
| 60° | 2807   |
| 65° | 2439   |
| 70° | 2180   |
| 75° | 2203   |
| 80° | 1642   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6326 cd/sqm

TEST NUMBER: P1280951

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1MW\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 42.0   | 16.0      |
| 10°-20°   | 77.5   | 29.6      |
| 20°-30°   | 69.0   | 26.3      |
| 30°-40°   | 40.8   | 15.6      |
| 40°-50°   | 16.7   | 6.4       |
| 50°-60°   | 7.9    | 3.0       |
| 60°-70°   | 4.8    | 1.8       |
| 70°-80°   | 2.5    | 1.0       |
| 80°-90°   | 0.6    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 188.6  | 72.0      |
| 0°-40°    | 229.4  | 87.6      |
| 0°-60°    | 254.0  | 97.0      |
| 0°-90°    | 262.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 262.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 515 |      |
| 5°  | 474 | 42   |
| 15° | 277 | 78   |
| 25° | 151 | 69   |
| 35° | 64  | 41   |
| 45° | 20  | 17   |
| 55° | 8   | 8    |
| 65° | 5   | 5    |
| 75° | 3   | 3    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1280951

CATALOG NUMBER: P3AS05R15B2750DE010 E3DLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 515.2 |
| 1°    | 514.0 |
| 2°    | 510.1 |
| 3°    | 502.5 |
| 4°    | 489.7 |
| 5°    | 474.4 |
| 6°    | 457.8 |
| 7°    | 438.2 |
| 8°    | 417.8 |
| 9°    | 397.0 |
| 10°   | 374.4 |
| 12.5° | 322.9 |
| 15°   | 277.4 |
| 17.5° | 238.3 |
| 20°   | 205.5 |
| 22.5° | 176.6 |
| 25°   | 151.0 |
| 27.5° | 126.4 |
| 30°   | 103.4 |
| 32.5° | 82.5  |
| 35°   | 63.8  |
| 37.5° | 48.9  |
| 40°   | 36.6  |
| 42.5° | 27.2  |
| 45°   | 20.4  |
| 47.5° | 15.7  |
| 50°   | 12.3  |
| 52.5° | 10.2  |
| 55°   | 8.5   |
| 57.5° | 7.2   |
| 60°   | 6.4   |
| 62.5° | 5.5   |
| 65°   | 4.7   |
| 67.5° | 4.3   |
| 70°   | 3.4   |
| 72.5° | 3.0   |
| 75°   | 2.6   |
| 77.5° | 1.7   |
| 80°   | 1.3   |
| 82.5° | 0.9   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)