

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282048

Luminaire Tested: P3AS05R55B2750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3DL1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 427.1 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282048

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282048

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82	79	77	75
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78	75	72	70
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63	62
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67	62	59	58
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63	59	56	55
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117249
5°	116068
10°	112089
15°	103610
20°	89398
25°	70601
30°	50084
35°	32310
40°	19408
45°	10947
50°	5868
55°	2103
60°	1886
65°	1816
70°	1731
75°	1694
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10947 cd/sqm

TEST NUMBER: P1282048

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	11.6
10°-20°	126.2	29.6
20°-30°	132.2	31.0
30°-40°	77.2	18.1
40°-50°	28.9	6.8
50°-60°	6.8	1.6
60°-70°	3.5	0.8
70°-80°	2.1	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.0	72.1
0°-40°	385.2	90.2
0°-60°	420.9	98.6
0°-90°	427.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	427.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	535	
5°	527	50
15°	456	126
25°	292	132
35°	121	77
45°	35	29
55°	6	7
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1282048

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	534.7
2.5°	533.1
5°	527.3
7.5°	517.9
10°	503.4
12.5°	483.0
15°	456.4
17.5°	422.7
20°	383.1
22.5°	338.8
25°	291.8
27.5°	243.7
30°	197.8
32.5°	156.3
35°	120.7
37.5°	91.7
40°	67.8
42.5°	48.6
45°	35.3
47.5°	25.5
50°	17.2
52.5°	9.8
55°	5.5
57.5°	4.7
60°	4.3
62.5°	3.9
65°	3.5
67.5°	3.1
70°	2.7
72.5°	2.4
75°	2.0
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)