

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282066

Luminaire Tested: P3AS05R55B2750DE010 E3DL1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55B2750DE010 E3DL1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 462.9 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282066

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282066

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	95	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127139
5°	125842
10°	121530
15°	112328
20°	96935
25°	76553
30°	54312
35°	35014
40°	21039
45°	11846
50°	6379
55°	2256
60°	2061
65°	1972
70°	1923
75°	1779
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11846 cd/sqm

TEST NUMBER: P1282066

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	11.6
10°-20°	136.8	29.6
20°-30°	143.4	31.0
30°-40°	83.7	18.1
40°-50°	31.3	6.8
50°-60°	7.4	1.6
60°-70°	3.8	0.8
70°-80°	2.2	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.0	72.1
0°-40°	417.7	90.2
0°-60°	456.3	98.6
0°-90°	462.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	462.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	580	
5°	572	54
15°	495	137
25°	316	143
35°	131	84
45°	38	31
55°	6	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1282066

CATALOG NUMBER: P3AS05R55B2750DE010 E3DL1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	579.8
2.5°	578.1
5°	571.7
7.5°	561.5
10°	545.8
12.5°	523.7
15°	494.8
17.5°	458.3
20°	415.4
22.5°	367.4
25°	316.4
27.5°	264.2
30°	214.5
32.5°	169.5
35°	130.8
37.5°	99.4
40°	73.5
42.5°	52.7
45°	38.2
47.5°	27.6
50°	18.7
52.5°	10.6
55°	5.9
57.5°	5.1
60°	4.7
62.5°	4.2
65°	3.8
67.5°	3.4
70°	3.0
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.3
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)