

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281052

Luminaire Tested: P3AS05R20B2750DE010 E3DL1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20B2750DE010 E3DL1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 411.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281052

CATALOG NUMBER: P3AS05R20B2750DE010 E3DL1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281052

CATALOG NUMBER: P3AS05R20B2750DE010 E3DL1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95						
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91						
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87						
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83						
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79						
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76						
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73						
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71						
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68						
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316225
5°	287452
10°	212443
15°	131420
20°	75047
25°	42849
30°	24029
35°	13063
40°	7156
45°	3938
50°	2286
55°	1682
60°	1579
65°	1453
70°	1282
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3938 cd/sqm

TEST NUMBER: P1281052

CATALOG NUMBER: P3AS05R20B2750DE010 E3DL1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	27.5
10°-20°	161.4	39.3
20°-30°	84.3	20.5
30°-40°	32.6	7.9
40°-50°	10.6	2.6
50°-60°	4.2	1.0
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.8	87.3
0°-40°	391.3	95.2
0°-60°	406.1	98.8
0°-90°	411.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	411.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1442	
5°	1306	113
15°	579	161
25°	177	84
35°	49	33
45°	13	11
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1281052

CATALOG NUMBER: P3AS05R20B2750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1442.1
1°	1439.3
2°	1422.2
3°	1396.0
4°	1355.5
5°	1305.9
6°	1247.1
7°	1182.0
8°	1106.6
9°	1033.1
10°	954.1
12.5°	758.4
15°	578.9
17.5°	433.2
20°	321.6
22.5°	238.2
25°	177.1
27.5°	130.6
30°	94.9
32.5°	68.7
35°	48.8
37.5°	35.3
40°	25.0
42.5°	17.9
45°	12.7
47.5°	9.1
50°	6.7
52.5°	5.2
55°	4.4
57.5°	4.0
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)