

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281068

Luminaire Tested: P3AS05R20B2750DE010 E3DLD1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20B2750DE010 E3DLD1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281068

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLD1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281068

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLD1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76178
5°	74158
10°	68202
15°	60046
20°	51501
25°	43261
30°	34967
35°	26609
40°	18921
45°	12497
50°	7744
55°	5085
60°	4649
65°	4255
70°	4039
75°	3643
80°	3410
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12497 cd/sqm

TEST NUMBER: P1281068

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLD1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.2	10.1
10°-20°	73.6	23.9
20°-30°	81.7	26.5
30°-40°	62.3	20.2
40°-50°	31.9	10.4
50°-60°	13.1	4.3
60°-70°	8.2	2.7
70°-80°	4.6	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.5	60.6
0°-40°	248.9	80.8
0°-60°	293.9	95.4
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	347	
5°	337	31
15°	264	74
25°	179	82
35°	99	62
45°	40	32
55°	13	13
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1281068

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLD1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	347.4
1°	347.8
2°	346.3
3°	344.3
4°	341.2
5°	336.9
6°	331.8
7°	326.3
8°	320.4
9°	313.4
10°	306.3
12.5°	286.0
15°	264.5
17.5°	242.6
20°	220.7
22.5°	198.8
25°	178.8
27.5°	158.8
30°	138.1
32.5°	118.5
35°	99.4
37.5°	82.6
40°	66.1
42.5°	52.0
45°	40.3
47.5°	30.5
50°	22.7
52.5°	16.8
55°	13.3
57.5°	12.1
60°	10.6
62.5°	9.4
65°	8.2
67.5°	7.0
70°	6.3
72.5°	5.1
75°	4.3
77.5°	3.5
80°	2.7
82.5°	2.0
85°	1.2
87.5°	0.4
90°	0.0

(END OF REPORT)