

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281088

Luminaire Tested: P3AS05R20B2750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20B2750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 405.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281088

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281088

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	311598
5°	283248
10°	209348
15°	129490
20°	73950
25°	42220
30°	23675
35°	12876
40°	7042
45°	3876
50°	2286
55°	1644
60°	1535
65°	1401
70°	1282
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3876 cd/sqm

TEST NUMBER: P1281088

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	27.5
10°-20°	159.1	39.3
20°-30°	83.0	20.5
30°-40°	32.1	7.9
40°-50°	10.4	2.6
50°-60°	4.1	1.0
60°-70°	2.7	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.5	87.3
0°-40°	385.6	95.2
0°-60°	400.1	98.8
0°-90°	405.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	405.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1421	
5°	1287	111
15°	570	159
25°	174	83
35°	48	32
45°	12	10
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1281088

CATALOG NUMBER: P3AS05R20B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1421.0
1°	1418.3
2°	1401.5
3°	1375.6
4°	1335.7
5°	1286.8
6°	1228.9
7°	1164.7
8°	1090.4
9°	1018.0
10°	940.2
12.5°	747.3
15°	570.4
17.5°	426.9
20°	316.9
22.5°	234.7
25°	174.5
27.5°	128.7
30°	93.5
32.5°	67.7
35°	48.1
37.5°	34.8
40°	24.6
42.5°	17.6
45°	12.5
47.5°	9.0
50°	6.7
52.5°	5.1
55°	4.3
57.5°	3.9
60°	3.5
62.5°	3.1
65°	2.7
67.5°	2.3
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)