

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282227

Luminaire Tested: P3AS05R60B2750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 327.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282227

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282227

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58044
5°	57385
10°	55399
15°	52350
20°	48258
25°	43696
30°	38791
35°	33140
40°	26364
45°	18576
50°	11087
55°	5620
60°	5394
65°	4929
70°	4552
75°	4406
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18576 cd/sqm

TEST NUMBER: P1282227

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.5	7.5
10°-20°	64.4	19.7
20°-30°	82.8	25.3
30°-40°	76.7	23.5
40°-50°	46.7	14.3
50°-60°	15.6	4.8
60°-70°	9.4	2.9
70°-80°	5.4	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.7	52.5
0°-40°	248.4	76.0
0°-60°	310.7	95.0
0°-90°	327.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	327.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	265	
5°	261	25
15°	231	64
25°	181	83
35°	124	77
45°	60	47
55°	15	16
65°	10	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1282227

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	264.7
2.5°	263.5
5°	260.7
7.5°	255.6
10°	248.8
12.5°	240.5
15°	230.6
17.5°	219.1
20°	206.8
22.5°	193.7
25°	180.6
27.5°	167.1
30°	153.2
32.5°	139.3
35°	123.8
37.5°	107.6
40°	92.1
42.5°	75.8
45°	59.9
47.5°	46.4
50°	32.5
52.5°	19.4
55°	14.7
57.5°	13.5
60°	12.3
62.5°	10.7
65°	9.5
67.5°	8.3
70°	7.1
72.5°	6.0
75°	5.2
77.5°	4.0
80°	3.2
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)