

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282238

Luminaire Tested: P3AS05R60B2750DE010 E3DLD1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1282238  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R60B2750DE010 E3DLD1WMH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 323.0 lumens  
Efficiency: N/A  
Efficacy: 54.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1282238  
CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1282238

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     | 0  |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 91  |    |    |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  | 91  | 88  | 85  | 88  | 86  | 84  | 82  |    |    |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 78  | 76  | 74  |    |    |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |    |    |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 61  |    |    |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |    |    |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  |    |    |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 47  |    |    |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  | 55  | 49  | 46  | 54  | 49  | 45  | 44  |    |    |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 57342 |
| 5°  | 56702 |
| 10° | 54731 |
| 15° | 51714 |
| 20° | 47651 |
| 25° | 43164 |
| 30° | 38310 |
| 35° | 32739 |
| 40° | 26020 |
| 45° | 18358 |
| 50° | 10951 |
| 55° | 5543  |
| 60° | 5350  |
| 65° | 4877  |
| 70° | 4552  |
| 75° | 4321  |
| 80° | 3915  |
| 85° | 3019  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18358 cd/sqm



TEST NUMBER: P1282238

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 24.2   | 7.5       |
| 10°-20°   | 63.7   | 19.7      |
| 20°-30°   | 81.7   | 25.3      |
| 30°-40°   | 75.8   | 23.5      |
| 40°-50°   | 46.1   | 14.3      |
| 50°-60°   | 15.4   | 4.8       |
| 60°-70°   | 9.4    | 2.9       |
| 70°-80°   | 5.3    | 1.6       |
| 80°-90°   | 1.5    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 169.6  | 52.5      |
| 0°-40°    | 245.4  | 76.0      |
| 0°-60°    | 306.9  | 95.0      |
| 0°-90°    | 323.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 323.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 262 |      |
| 5°  | 258 | 24   |
| 15° | 228 | 64   |
| 25° | 178 | 82   |
| 35° | 122 | 76   |
| 45° | 59  | 46   |
| 55° | 14  | 15   |
| 65° | 9   | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 2    |
| 90° | 0   |      |



TEST NUMBER: P1282238  
CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 261.5 |
| 2.5°  | 260.3 |
| 5°    | 257.6 |
| 7.5°  | 252.5 |
| 10°   | 245.8 |
| 12.5° | 237.6 |
| 15°   | 227.8 |
| 17.5° | 216.4 |
| 20°   | 204.2 |
| 22.5° | 191.3 |
| 25°   | 178.4 |
| 27.5° | 165.0 |
| 30°   | 151.3 |
| 32.5° | 137.6 |
| 35°   | 122.3 |
| 37.5° | 106.2 |
| 40°   | 90.9  |
| 42.5° | 74.9  |
| 45°   | 59.2  |
| 47.5° | 45.9  |
| 50°   | 32.1  |
| 52.5° | 19.2  |
| 55°   | 14.5  |
| 57.5° | 13.3  |
| 60°   | 12.2  |
| 62.5° | 10.6  |
| 65°   | 9.4   |
| 67.5° | 8.2   |
| 70°   | 7.1   |
| 72.5° | 5.9   |
| 75°   | 5.1   |
| 77.5° | 3.9   |
| 80°   | 3.1   |
| 82.5° | 2.0   |
| 85°   | 1.2   |
| 87.5° | 0.8   |
| 90°   | 0.0   |

(END OF REPORT)