

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281150

Luminaire Tested: P3AS05R25B2750DE010 E3D1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3D1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 507.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281150

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281150

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	109	108		107	106	105		103	103	102		100	99	99
2	112	108	105	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	108	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	90		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	87		99	93	90	87		92	89	87		91	88	86		90	87	86
7	97	91	88	85		96	91	87	85		90	87	84		89	86	84		88	85	83
8	95	89	85	83		94	89	85	82		88	84	82		87	84	82		86	83	81
9	93	87	83	80		92	86	83	80		86	82	80		85	82	80		84	82	80
10	91	85	81	78		90	84	81	78		84	80	78		83	80	78		82	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542062
5°	502750
10°	389884
15°	195506
20°	64219
25°	25550
30°	9571
35°	2784
40°	1260
45°	496
50°	409
55°	306
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 505 cd/sqm

TEST NUMBER: P1281150

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.9	39.6
10°-20°	239.7	47.3
20°-30°	54.0	10.7
30°-40°	8.8	1.7
40°-50°	1.6	0.3
50°-60°	0.8	0.2
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.6	97.5
0°-40°	503.4	99.3
0°-60°	505.8	99.8
0°-90°	507.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2472	
5°	2284	201
15°	861	240
25°	106	54
35°	10	9
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281150

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2472.0
1°	2468.0
2°	2448.1
3°	2411.4
4°	2356.1
5°	2284.0
6°	2197.9
7°	2104.7
8°	1998.0
9°	1881.3
10°	1751.0
11°	1600.8
12°	1428.0
13°	1247.1
14°	1053.2
15°	861.2
17.5°	490.7
20°	275.2
22.5°	166.1
25°	105.6
27.5°	64.9
30°	37.8
32.5°	19.9
35°	10.4
37.5°	6.8
40°	4.4
42.5°	2.8
45°	1.6
47.5°	1.2
50°	1.2
52.5°	1.2
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1281150

CATALOG NUMBER: P3AS05R25B2750DE010 E3D1MW_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)