

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282239

Luminaire Tested: P3AS05R60B2750DE010 E3DLD1WMH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3DLD1WMH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 331.0 lumens
Efficiency: N/A
Efficacy: 56.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282239

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1282239

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	101		102	100	98		99	97	95		95	94	93
2	105	99	94	90		103	98	93	89		94	90	87		91	88	85		88	86	84
3	99	91	85	80		96	89	84	79		87	82	78		84	80	77		82	78	76
4	92	83	77	72		90	82	76	71		80	75	71		78	73	70		76	72	69
5	87	77	70	65		85	76	69	65		74	68	64		72	67	63		71	66	63
6	82	71	64	59		80	70	64	59		69	63	58		67	62	58		66	61	58
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58	53	49
9	68	57	51	46		67	57	50	46		56	50	46		55	49	46		54	49	45
10	65	54	47	43		64	53	47	43		52	47	43		52	46	42		51	46	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58767
5°	58089
10°	56089
15°	52986
20°	48841
25°	44228
30°	39272
35°	33542
40°	26679
45°	18824
50°	11224
55°	5696
60°	5482
65°	4981
70°	4616
75°	4406
80°	4041
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18824 cd/sqm

TEST NUMBER: P1282239

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	7.5
10°-20°	65.2	19.7
20°-30°	83.8	25.3
30°-40°	77.7	23.5
40°-50°	47.3	14.3
50°-60°	15.8	4.8
60°-70°	9.6	2.9
70°-80°	5.4	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.8	52.5
0°-40°	251.4	76.0
0°-60°	314.5	95.0
0°-90°	331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	268	
5°	264	25
15°	233	65
25°	183	84
35°	125	78
45°	61	47
55°	15	16
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1282239

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLD1WMH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	268.0
2.5°	266.7
5°	263.9
7.5°	258.7
10°	251.9
12.5°	243.4
15°	233.4
17.5°	221.8
20°	209.3
22.5°	196.0
25°	182.8
27.5°	169.1
30°	155.1
32.5°	141.0
35°	125.3
37.5°	108.9
40°	93.2
42.5°	76.7
45°	60.7
47.5°	47.0
50°	32.9
52.5°	19.7
55°	14.9
57.5°	13.7
60°	12.5
62.5°	10.8
65°	9.6
67.5°	8.4
70°	7.2
72.5°	6.0
75°	5.2
77.5°	4.0
80°	3.2
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)