

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282268

Luminaire Tested: P3AS05R60B2750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60B2750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282268

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282268

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	94	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	86	86	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	80	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	73	73	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	68	68	66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	63	63	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	59	59	57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	55	55	54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	52	52	50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	49	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72231
5°	70614
10°	66109
15°	59297
20°	50988
25°	42172
30°	33322
35°	24735
40°	17032
45°	10699
50°	5868
55°	3441
60°	3070
65°	2646
70°	2244
75°	2288
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10699 cd/sqm

TEST NUMBER: P1282268

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.9	10.5
10°-20°	72.5	25.5
20°-30°	79.6	27.9
30°-40°	58.0	20.3
40°-50°	27.4	9.6
50°-60°	9.0	3.1
60°-70°	5.1	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.0	63.9
0°-40°	240.0	84.2
0°-60°	276.3	97.0
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	329	
5°	321	30
15°	261	73
25°	174	80
35°	92	58
45°	34	27
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1282268

CATALOG NUMBER: P3AS05R60B2750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	329.4
2.5°	327.4
5°	320.8
7.5°	310.6
10°	296.9
12.5°	280.4
15°	261.2
17.5°	240.5
20°	218.5
22.5°	196.2
25°	174.3
27.5°	152.4
30°	131.6
32.5°	111.6
35°	92.4
37.5°	75.2
40°	59.5
42.5°	45.8
45°	34.5
47.5°	25.1
50°	17.2
52.5°	11.4
55°	9.0
57.5°	7.8
60°	7.0
62.5°	5.9
65°	5.1
67.5°	4.3
70°	3.5
72.5°	3.1
75°	2.7
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)