

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282281

Luminaire Tested: P3AS05R65B2750DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282281
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3CB1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 526.1 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282281

CATALOG NUMBER: P3AS05R65B2750DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282281

CATALOG NUMBER: P3AS05R65B2750DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	81	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128542
5°	120977
10°	119437
15°	117345
20°	110773
25°	102829
30°	79911
35°	46230
40°	18635
45°	8590
50°	3343
55°	1300
60°	1140
65°	1090
70°	1090
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8590 cd/sqm

TEST NUMBER: P1282281

CATALOG NUMBER: P3AS05R65B2750DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.2	9.9
10°-20°	144.3	27.4
20°-30°	188.9	35.9
30°-40°	109.4	20.8
40°-50°	23.4	4.5
50°-60°	3.8	0.7
60°-70°	2.1	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.5	73.3
0°-40°	495.0	94.1
0°-60°	522.2	99.3
0°-90°	526.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	586	
5°	550	52
15°	517	144
25°	425	189
35°	173	109
45°	28	23
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282281

CATALOG NUMBER: P3AS05R65B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	586.2
2.5°	569.6
5°	549.6
7.5°	541.5
10°	536.4
12.5°	529.2
15°	516.9
17.5°	497.7
20°	474.7
22.5°	453.1
25°	425.0
27.5°	377.8
30°	315.6
32.5°	244.6
35°	172.7
37.5°	109.3
40°	65.1
42.5°	40.8
45°	27.7
47.5°	17.9
50°	9.8
52.5°	4.7
55°	3.4
57.5°	3.0
60°	2.6
62.5°	2.6
65°	2.1
67.5°	1.7
70°	1.7
72.5°	1.3
75°	1.3
77.5°	0.9
80°	0.9
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)