

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282320

Luminaire Tested: P3AS05R65B2750DE010 E3D1WH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3D1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 80CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282320

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282320

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	88	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	81	78	77
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127271
5°	118182
10°	114293
15°	110148
20°	101836
25°	92763
30°	71682
35°	41546
40°	16488
45°	7008
50°	1672
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7008 cd/sqm

TEST NUMBER: P1282320

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	10.7
10°-20°	135.2	28.5
20°-30°	171.1	36.0
30°-40°	97.4	20.5
40°-50°	19.4	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.9	75.1
0°-40°	454.4	95.7
0°-60°	474.7	99.9
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	580	
5°	537	51
15°	485	135
25°	383	171
35°	155	97
45°	23	19
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282320

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	580.4
1°	576.1
2°	566.8
3°	555.8
4°	545.1
5°	536.9
6°	530.8
7°	526.0
8°	521.7
9°	517.4
10°	513.3
11°	508.8
12°	504.1
13°	498.4
14°	492.4
15°	485.2
16°	476.6
17°	467.2
18°	457.1
19°	446.3
20°	436.4
21°	426.2
22°	417.0
23°	407.5
24°	396.3
25°	383.4
26°	368.0
27°	349.5
28°	328.6
29°	306.3
30°	283.1
31°	257.5
32°	232.1
32.5°	219.1
33°	206.4
34°	180.6
35°	155.2
36°	131.8
37°	108.6
37.5°	96.6
38°	87.1
39°	70.5
40°	57.6
42.5°	35.5
45°	22.6



TEST NUMBER: P1282320

CATALOG NUMBER: P3AS05R65B2750DE010 E3D1WH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.3
50°	4.9
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)