

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281185

Luminaire Tested: P3AS05R25B2750DE010 E3DL1WH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1281185  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R25B2750DE010 E3DL1WH\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 255.0 lumens  
Efficiency: N/A  
Efficacy: 43.2 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281185  
CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1WH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1281185  
 CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92580
5°	88818
10°	77799
15°	62543
20°	48048
25°	36365
30°	26283
35°	17454
40°	10591
45°	6171
50°	3923
55°	3173
60°	2807
65°	2491
70°	2052
75°	2033
80°	1515
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6171 cd/sqm



TEST NUMBER: P1281185

CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.7	14.4
10°-20°	76.2	29.9
20°-30°	68.9	27.0
30°-40°	41.4	16.2
40°-50°	16.4	6.4
50°-60°	7.6	3.0
60°-70°	4.6	1.8
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.8	71.3
0°-40°	223.2	87.5
0°-60°	247.2	96.9
0°-90°	255.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	255.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	422	
5°	404	37
15°	276	76
25°	150	69
35°	65	41
45°	20	16
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1281185  
CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	422.2
1°	422.2
2°	420.2
3°	415.8
4°	410.3
5°	403.5
6°	394.8
7°	384.8
8°	373.3
9°	361.8
10°	349.4
11°	335.1
12°	320.4
13°	305.7
14°	291.0
15°	275.5
17.5°	238.9
20°	205.9
22.5°	176.1
25°	150.3
27.5°	126.0
30°	103.8
32.5°	83.5
35°	65.2
37.5°	49.7
40°	37.0
42.5°	27.0
45°	19.9
47.5°	15.1
50°	11.5
52.5°	9.5
55°	8.3
57.5°	7.2
60°	6.4
62.5°	5.2
65°	4.8
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1281185  
CATALOG NUMBER: P3AS05R25B2750DE010 E3DL1WH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)