

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281238

Luminaire Tested: P3AS05R25B2750DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25B2750DE010 E3DLP1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 42.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281238

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281238

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91133
5°	87431
10°	76596
15°	61567
20°	47301
25°	35784
30°	25852
35°	17186
40°	10420
45°	6078
50°	3855
55°	3135
60°	2763
65°	2439
70°	1988
75°	1949
80°	1515
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6078 cd/sqm

TEST NUMBER: P1281238

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	14.4
10°-20°	75.0	29.9
20°-30°	67.8	27.0
30°-40°	40.7	16.2
40°-50°	16.2	6.4
50°-60°	7.4	3.0
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	179.0	71.3
0°-40°	219.7	87.5
0°-60°	243.3	96.9
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	416	
5°	397	36
15°	271	75
25°	148	68
35°	64	41
45°	20	16
55°	8	7
65°	5	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1281238

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	415.6
1°	415.6
2°	413.6
3°	409.3
4°	403.8
5°	397.2
6°	388.6
7°	378.8
8°	367.4
9°	356.1
10°	344.0
11°	329.9
12°	315.4
13°	300.9
14°	286.4
15°	271.2
17.5°	235.2
20°	202.7
22.5°	173.4
25°	147.9
27.5°	124.0
30°	102.1
32.5°	82.2
35°	64.2
37.5°	48.9
40°	36.4
42.5°	26.6
45°	19.6
47.5°	14.9
50°	11.3
52.5°	9.4
55°	8.2
57.5°	7.0
60°	6.3
62.5°	5.1
65°	4.7
67.5°	3.9
70°	3.1
72.5°	2.7
75°	2.3
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1281238

CATALOG NUMBER: P3AS05R25B2750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)