

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282378

Luminaire Tested: P3AS05R65B2750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282378

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282378

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91											
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82											
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67											
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56											
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51											
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47											
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44											
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54820
5°	54083
10°	52259
15°	49285
20°	45457
25°	41252
30°	36537
35°	31106
40°	24732
45°	17459
50°	10132
55°	5543
60°	5131
65°	4670
70°	4231
75°	3982
80°	3410
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17459 cd/sqm

TEST NUMBER: P1282378

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	7.5
10°-20°	60.7	19.7
20°-30°	78.0	25.3
30°-40°	72.2	23.4
40°-50°	43.6	14.1
50°-60°	14.9	4.8
60°-70°	8.9	2.9
70°-80°	5.0	1.6
80°-90°	1.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.9	52.6
0°-40°	234.1	76.0
0°-60°	292.5	95.0
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	250	
5°	246	23
15°	217	61
25°	170	78
35°	116	72
45°	56	44
55°	14	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1282378

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	250.0
2.5°	248.8
5°	245.7
7.5°	241.0
10°	234.7
12.5°	226.9
15°	217.1
17.5°	206.5
20°	194.8
22.5°	182.7
25°	170.5
27.5°	157.6
30°	144.3
32.5°	131.0
35°	116.2
37.5°	101.7
40°	86.4
42.5°	71.2
45°	56.3
47.5°	42.6
50°	29.7
52.5°	18.8
55°	14.5
57.5°	12.9
60°	11.7
62.5°	10.2
65°	9.0
67.5°	7.8
70°	6.6
72.5°	5.9
75°	4.7
77.5°	3.9
80°	2.7
82.5°	2.0
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)