

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282389

Luminaire Tested: P3AS05R65B2750DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 136.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282389

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1282389

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34559
5°	33700
10°	31396
15°	28127
20°	24292
25°	20203
30°	15927
35°	11805
40°	8130
45°	5055
50°	2729
55°	1720
60°	1447
65°	1297
70°	1154
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5055 cd/sqm

TEST NUMBER: P1282389

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.2	10.5
10°-20°	34.4	25.3
20°-30°	38.1	28.0
30°-40°	27.7	20.3
40°-50°	13.0	9.5
50°-60°	4.3	3.2
60°-70°	2.5	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	86.7	63.8
0°-40°	114.4	84.1
0°-60°	131.7	96.8
0°-90°	136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	136.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	158	
5°	153	14
15°	124	34
25°	84	38
35°	44	28
45°	16	13
55°	4	4
65°	2	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282389

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	157.6
2.5°	156.7
5°	153.1
7.5°	147.8
10°	141.0
12.5°	132.9
15°	123.9
17.5°	114.1
20°	104.1
22.5°	93.7
25°	83.5
27.5°	73.1
30°	62.9
32.5°	53.1
35°	44.1
37.5°	35.9
40°	28.4
42.5°	21.8
45°	16.3
47.5°	11.8
50°	8.0
52.5°	5.5
55°	4.5
57.5°	3.9
60°	3.3
62.5°	2.9
65°	2.5
67.5°	2.2
70°	1.8
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)