

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281373

Luminaire Tested: P3AS05R30B2750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 319.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281373

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281373

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75367
5°	73674
10°	68514
15°	60954
20°	52435
25°	44422
30°	36866
35°	28911
40°	20725
45°	13583
50°	7744
55°	5085
60°	4824
65°	4462
70°	4039
75°	3643
80°	3410
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13583 cd/sqm

TEST NUMBER: P1281373

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.1	9.7
10°-20°	74.6	23.4
20°-30°	84.1	26.4
30°-40°	67.2	21.1
40°-50°	34.5	10.8
50°-60°	13.0	4.1
60°-70°	8.5	2.7
70°-80°	4.6	1.4
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.9	59.5
0°-40°	257.0	80.6
0°-60°	304.5	95.5
0°-90°	319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	344	
5°	335	31
15°	268	75
25°	184	84
35°	108	67
45°	44	35
55°	13	13
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1281373

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	343.7
1°	343.7
2°	342.5
3°	340.6
4°	337.8
5°	334.7
6°	330.8
7°	325.7
8°	320.2
9°	313.9
10°	307.7
11°	300.6
12°	293.2
13°	285.4
14°	277.1
15°	268.5
17.5°	246.6
20°	224.7
22.5°	203.6
25°	183.6
27.5°	164.0
30°	145.6
32.5°	126.8
35°	108.0
37.5°	89.6
40°	72.4
42.5°	57.2
45°	43.8
47.5°	32.5
50°	22.7
52.5°	16.0
55°	13.3
57.5°	12.1
60°	11.0
62.5°	9.8
65°	8.6
67.5°	7.4
70°	6.3
72.5°	5.1
75°	4.3
77.5°	3.5
80°	2.7
82.5°	2.0
85°	1.2
87.5°	0.4



TEST NUMBER: P1281373

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)