

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282413

Luminaire Tested: P3AS05R65B2750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65B2750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 271.0 lumens
Efficiency: N/A
Efficacy: 45.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282413

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282413

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94		92			
2	107	101	97	93		104	100	96	92		96	93	90		93	91	88		90	88	86		85			
3	101	94	88	84		99	92	87	83		90	85	82		87	84	81		85	82	79		78			
4	95	87	81	76		93	86	80	76		84	79	75		82	78	74		80	76	73		72			
5	90	81	75	70		88	80	74	70		78	73	69		77	72	69		75	71	68		66			
6	85	76	69	65		84	75	69	65		73	68	64		72	67	64		71	66	63		62			
7	81	71	65	60		79	70	64	60		69	64	60		68	63	59		67	62	59		57			
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55		54			
9	73	63	57	52		72	62	56	52		61	56	52		60	55	52		59	55	52		50			
10	69	59	53	49		68	59	53	49		58	53	49		57	52	49		56	52	49		47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68876
5°	67158
10°	62546
15°	56050
20°	48421
25°	40260
30°	31752
35°	23530
40°	16230
45°	10048
50°	5458
55°	3441
60°	2895
65°	2646
70°	2244
75°	1949
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10048 cd/sqm

TEST NUMBER: P1282413

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.4	10.5
10°-20°	68.6	25.3
20°-30°	75.9	28.0
30°-40°	55.1	20.3
40°-50°	25.8	9.5
50°-60°	8.7	3.2
60°-70°	5.0	1.9
70°-80°	2.6	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.9	63.8
0°-40°	228.0	84.1
0°-60°	262.5	96.9
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	305	28
15°	247	69
25°	166	76
35°	88	55
45°	32	26
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1282413

CATALOG NUMBER: P3AS05R65B2750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	314.1
2.5°	312.2
5°	305.1
7.5°	294.6
10°	280.9
12.5°	264.9
15°	246.9
17.5°	227.4
20°	207.5
22.5°	186.8
25°	166.4
27.5°	145.7
30°	125.4
32.5°	105.9
35°	87.9
37.5°	71.5
40°	56.7
42.5°	43.4
45°	32.4
47.5°	23.4
50°	16.0
52.5°	10.9
55°	9.0
57.5°	7.8
60°	6.6
62.5°	5.9
65°	5.1
67.5°	4.3
70°	3.5
72.5°	3.1
75°	2.3
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)