

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281397

Luminaire Tested: P3AS05R30B2750DE010 E3DLP1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3DLP1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281397

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281397

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87471
5°	84746
10°	76374
15°	63179
20°	48911
25°	36680
30°	26637
35°	17748
40°	10906
45°	6388
50°	3923
55°	3173
60°	2807
65°	2283
70°	2052
75°	2033
80°	1515
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6388 cd/sqm

TEST NUMBER: P1281397

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.4	13.8
10°-20°	76.6	29.9
20°-30°	69.7	27.2
30°-40°	42.1	16.5
40°-50°	16.9	6.6
50°-60°	7.5	2.9
60°-70°	4.5	1.8
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.8	71.0
0°-40°	223.9	87.5
0°-60°	248.3	97.0
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	399	
5°	385	35
15°	278	77
25°	152	70
35°	66	42
45°	21	17
55°	8	7
65°	4	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1281397

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	398.9
1°	398.5
2°	397.0
3°	394.2
4°	390.2
5°	385.0
6°	378.7
7°	371.9
8°	363.2
9°	353.3
10°	343.0
11°	331.1
12°	318.4
13°	305.7
14°	291.8
15°	278.3
17.5°	242.9
20°	209.6
22.5°	178.6
25°	151.6
27.5°	127.0
30°	105.2
32.5°	84.9
35°	66.3
37.5°	50.8
40°	38.1
42.5°	27.8
45°	20.6
47.5°	15.5
50°	11.5
52.5°	9.1
55°	8.3
57.5°	7.1
60°	6.4
62.5°	5.2
65°	4.4
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1281397

CATALOG NUMBER: P3AS05R30B2750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)