

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281412

Luminaire Tested: P3AS05R30B2750DE010 E3PH1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3PH1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 409.0 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281412
CATALOG NUMBER: P3AS05R30B2750DE010 E3PH1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281412
 CATALOG NUMBER: P3AS05R30B2750DE010 E3PH1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99		97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96		95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94		93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	92	95	93	91		90
5	104	98	95	92	102	97	94	91	96	93	91	94	92	90	93	91	89		88
6	101	95	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87		86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85		84
8	96	91	87	84	96	90	87	84	89	86	84	88	86	84	88	85	83		83
9	94	89	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82		81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80		79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	582146
5°	508517
10°	278975
15°	128355
20°	69166
25°	23445
30°	3038
35°	455
40°	172
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1281412

CATALOG NUMBER: P3AS05R30B2750DE010 E3PH1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.1	45.3
10°-20°	169.6	41.5
20°-30°	52.2	12.8
30°-40°	1.9	0.5
40°-50°	0.2	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.9	99.5
0°-40°	408.8	100.0
0°-60°	409.0	100.0
0°-90°	409.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	409.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2655	
5°	2310	185
15°	565	170
25°	97	52
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1281412
CATALOG NUMBER: P3AS05R30B2750DE010 E3PH1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2654.8
2.5°	2592.9
5°	2310.2
7.5°	1812.5
10°	1252.9
12.5°	848.1
15°	565.4
17.5°	396.2
20°	296.4
22.5°	199.5
25°	96.9
27.5°	35.6
30°	12.0
32.5°	4.0
35°	1.7
37.5°	1.1
40°	0.6
42.5°	0.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)