

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281426

Luminaire Tested: P3AS05R30B2750DE010 E3PHLP1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30B2750DE010 E3PHLP1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 239.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281426

CATALOG NUMBER: P3AS05R30B2750DE010 E3PHLP1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281426

CATALOG NUMBER: P3AS05R30B2750DE010 E3PHLP1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	88	78	72	67	86	77	71	66	76	70	66	74	69	65	72	68	65	63		
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59		
7	79	69	62	58	78	68	62	57	67	61	57	66	60	57	64	60	56	55		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77603
5°	73167
10°	62546
15°	50125
20°	39063
25°	29373
30°	21421
35°	15098
40°	10362
45°	7412
50°	6072
55°	5849
60°	5921
65°	6071
70°	6283
75°	6778
80°	6945
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 8232 cd/sqm

TEST NUMBER: P1281426

CATALOG NUMBER: P3AS05R30B2750DE010 E3PHLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.1	12.6
10°-20°	61.3	25.7
20°-30°	55.9	23.4
30°-40°	35.6	14.9
40°-50°	19.0	8.0
50°-60°	13.9	5.8
60°-70°	11.7	4.9
70°-80°	8.2	3.4
80°-90°	3.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	147.3	61.6
0°-40°	182.9	76.5
0°-60°	215.9	90.3
0°-90°	239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	239.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	354	
5°	332	30
15°	221	61
25°	121	56
35°	56	36
45°	24	19
55°	15	14
65°	12	12
75°	8	8
85°	3	3
90°	0	



TEST NUMBER: P1281426

CATALOG NUMBER: P3AS05R30B2750DE010 E3PHLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	353.9
2.5°	348.4
5°	332.4
7.5°	309.1
10°	280.9
12.5°	250.8
15°	220.8
17.5°	193.2
20°	167.4
22.5°	143.5
25°	121.4
27.5°	101.8
30°	84.6
32.5°	68.7
35°	56.4
37.5°	44.8
40°	36.2
42.5°	28.8
45°	23.9
47.5°	19.6
50°	17.8
52.5°	16.6
55°	15.3
57.5°	14.7
60°	13.5
62.5°	12.9
65°	11.7
67.5°	11.0
70°	9.8
72.5°	8.6
75°	8.0
77.5°	6.7
80°	5.5
82.5°	4.9
85°	3.1
87.5°	1.2
90°	0.0

(END OF REPORT)