

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281443

Luminaire Tested: P3AS05R35B2750DE010 E3CD1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281443
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3CD1MB_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 497.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281443

CATALOG NUMBER: P3AS05R35B2750DE010 E3CD1MB_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281443

CATALOG NUMBER: P3AS05R35B2750DE010 E3CD1MB_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98		96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94		93
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94	92	90		89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87		86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84		83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81		80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79		77
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76		75
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79	76	74		73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	71		70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324075
5°	317477
10°	295341
15°	216528
20°	110890
25°	39970
30°	15547
35°	5461
40°	2233
45°	620
50°	546
55°	612
60°	526
65°	415
70°	513
75°	678
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 678 cd/sqm

TEST NUMBER: P1281443

CATALOG NUMBER: P3AS05R35B2750DE010 E3CD1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	27.0
10°-20°	252.3	50.8
20°-30°	89.3	18.0
30°-40°	15.6	3.1
40°-50°	2.3	0.5
50°-60°	1.3	0.3
60°-70°	0.9	0.2
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.1	95.8
0°-40°	491.7	98.9
0°-60°	495.3	99.6
0°-90°	497.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1478	
5°	1442	134
15°	954	252
25°	165	89
35°	20	16
45°	2	2
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1281443

CATALOG NUMBER: P3AS05R35B2750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1477.9
1°	1477.5
2°	1472.8
3°	1463.8
4°	1455.6
5°	1442.3
6°	1428.6
7°	1413.3
8°	1394.5
9°	1365.2
10°	1326.4
11°	1272.8
12°	1208.2
13°	1131.5
14°	1047.0
15°	953.8
17.5°	710.4
20°	475.2
22.5°	286.5
25°	165.2
27.5°	98.6
30°	61.4
32.5°	35.6
35°	20.4
37.5°	12.9
40°	7.8
42.5°	3.9
45°	2.0
47.5°	1.6
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0



TEST NUMBER: P1281443

CATALOG NUMBER: P3AS05R35B2750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)