

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282463

Luminaire Tested: P3AS05R70B2750DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3D1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 467.1 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282463

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282463

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	76	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90804
5°	85626
10°	81183
15°	79728
20°	76843
25°	72440
30°	71935
35°	62640
40°	40533
45°	19165
50°	2695
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19165 cd/sqm

TEST NUMBER: P1282463

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	7.8
10°-20°	98.6	21.1
20°-30°	139.5	29.9
30°-40°	140.2	30.0
40°-50°	50.4	10.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.5	58.8
0°-40°	414.7	88.8
0°-60°	466.5	99.9
0°-90°	467.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	467.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	389	36
15°	351	99
25°	299	140
35°	234	140
45°	62	50
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1282463

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.1
1°	413.0
2°	409.3
3°	403.6
4°	396.3
5°	389.0
6°	382.1
7°	376.7
8°	371.9
9°	368.1
10°	364.6
11°	361.7
12°	359.1
13°	356.4
14°	353.9
15°	351.2
16°	347.9
17°	344.5
18°	340.3
19°	335.1
20°	329.3
21°	323.0
22°	316.7
23°	310.5
24°	304.6
25°	299.4
26°	295.8
27°	292.9
28°	290.6
29°	287.9
30°	284.1
31°	278.5
32°	270.6
32.5°	266.2
33°	260.3
34°	248.6
35°	234.0
36°	217.9
37°	199.7
37.5°	191.2
38°	179.7
39°	159.2
40°	141.6
42.5°	98.0
45°	61.8



TEST NUMBER: P1282463

CATALOG NUMBER: P3AS05R70B2750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	33.2
50°	7.9
52.5°	1.0
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)