

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281463

Luminaire Tested: P3AS05R35B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 202.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281463

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281463

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	90	88	86	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70		
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66		
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64		
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101878
5°	97909
10°	85302
15°	65335
20°	43707
25°	26445
30°	15167
35°	8486
40°	4523
45°	2326
50°	1126
55°	879
60°	833
65°	675
70°	769
75°	678
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2326 cd/sqm

TEST NUMBER: P1281463

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	20.0
10°-20°	78.4	38.8
20°-30°	51.3	25.4
30°-40°	20.8	10.3
40°-50°	6.3	3.1
50°-60°	2.1	1.0
60°-70°	1.4	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.2	84.3
0°-40°	191.1	94.6
0°-60°	199.5	98.7
0°-90°	202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	202.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	465	
5°	445	40
15°	288	78
25°	109	51
35°	32	21
45°	8	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281463

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	464.6
1°	463.8
2°	461.7
3°	457.5
4°	452.5
5°	444.8
6°	435.2
7°	424.5
8°	412.3
9°	398.5
10°	383.1
11°	366.0
12°	348.2
13°	328.2
14°	309.2
15°	287.8
17.5°	236.1
20°	187.3
22.5°	144.1
25°	109.3
27.5°	81.5
30°	59.9
32.5°	44.0
35°	31.7
37.5°	22.5
40°	15.8
42.5°	11.0
45°	7.5
47.5°	5.0
50°	3.3
52.5°	2.5
55°	2.3
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.3
67.5°	1.2
70°	1.2
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1281463

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)