

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282501

Luminaire Tested: P3AS05R70B2750DE010 E3DL1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3DL1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 428.1 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282501

CATALOG NUMBER: P3AS05R70B2750DE010 E3DL1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282501

CATALOG NUMBER: P3AS05R70B2750DE010 E3DL1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82866
5°	81862
10°	79491
15°	76141
20°	71313
25°	64794
30°	55958
35°	44598
40°	32489
45°	21367
50°	9995
55°	3097
60°	2982
65°	2854
70°	2757
75°	2881
80°	2652
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21367 cd/sqm

TEST NUMBER: P1282501

CATALOG NUMBER: P3AS05R70B2750DE010 E3DL1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	8.2
10°-20°	93.9	21.9
20°-30°	122.0	28.5
30°-40°	103.5	24.2
40°-50°	53.4	12.5
50°-60°	10.3	2.4
60°-70°	5.6	1.3
70°-80°	3.4	0.8
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.9	58.6
0°-40°	354.4	82.8
0°-60°	418.1	97.7
0°-90°	428.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	428.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	378	
5°	372	35
15°	335	94
25°	268	122
35°	167	103
45°	69	53
55°	8	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1282501

CATALOG NUMBER: P3AS05R70B2750DE010 E3DL1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	377.9
2.5°	376.6
5°	371.9
7.5°	365.1
10°	357.0
12.5°	346.8
15°	335.4
17.5°	321.3
20°	305.6
22.5°	287.8
25°	267.8
27.5°	245.2
30°	221.0
32.5°	194.2
35°	166.6
37.5°	139.4
40°	113.5
42.5°	89.3
45°	68.9
47.5°	50.6
50°	29.3
52.5°	12.8
55°	8.1
57.5°	7.7
60°	6.8
62.5°	6.4
65°	5.5
67.5°	5.1
70°	4.3
72.5°	3.8
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)