

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281487

Luminaire Tested: P3AS05R35B2750DE010 E3DL1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3DL1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 417.1 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281487

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1281487

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	70
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74	70	68	66
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210312
5°	202135
10°	176105
15°	134893
20°	90238
25°	54608
30°	31347
35°	17507
40°	9303
45°	4807
50°	2286
55°	1835
60°	1754
65°	1453
70°	1539
75°	1356
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4807 cd/sqm

TEST NUMBER: P1281487

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	20.0
10°-20°	161.9	38.8
20°-30°	106.0	25.4
30°-40°	43.0	10.3
40°-50°	12.9	3.1
50°-60°	4.4	1.1
60°-70°	3.0	0.7
70°-80°	1.7	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.5	84.3
0°-40°	394.4	94.6
0°-60°	411.7	98.7
0°-90°	417.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	417.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	959	
5°	918	84
15°	594	162
25°	226	106
35°	65	43
45°	16	13
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1281487

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	959.1
1°	957.5
2°	953.2
3°	944.4
4°	934.1
5°	918.3
6°	898.4
7°	876.2
8°	851.2
9°	822.7
10°	790.9
11°	755.6
12°	718.7
13°	677.5
14°	638.2
15°	594.2
17.5°	487.5
20°	386.7
22.5°	297.5
25°	225.7
27.5°	168.2
30°	123.8
32.5°	90.8
35°	65.4
37.5°	46.4
40°	32.5
42.5°	22.6
45°	15.5
47.5°	10.3
50°	6.7
52.5°	5.2
55°	4.8
57.5°	4.4
60°	4.0
62.5°	3.6
65°	2.8
67.5°	2.4
70°	2.4
72.5°	2.0
75°	1.6
77.5°	1.2
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1281487

CATALOG NUMBER: P3AS05R35B2750DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)