

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281516

Luminaire Tested: P3AS05R35B2750DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1281516  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R35B2750DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 344.1 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1281516

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1281516

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 83  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 75  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  |  | 62  | 56  | 53  |  | 61  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 78590 |
| 5°  | 76909 |
| 10° | 72032 |
| 15° | 64654 |
| 20° | 56238 |
| 25° | 47930 |
| 30° | 40158 |
| 35° | 31989 |
| 40° | 23129 |
| 45° | 14637 |
| 50° | 7983  |
| 55° | 5543  |
| 60° | 5219  |
| 65° | 4877  |
| 70° | 4616  |
| 75° | 3982  |
| 80° | 3788  |
| 85° | 3271  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14637 cd/sqm

TEST NUMBER: P1281516

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 32.5   | 9.5       |
| 10°-20°   | 79.3   | 23.0      |
| 20°-30°   | 90.8   | 26.4      |
| 30°-40°   | 74.1   | 21.5      |
| 40°-50°   | 37.4   | 10.9      |
| 50°-60°   | 13.9   | 4.0       |
| 60°-70°   | 9.3    | 2.7       |
| 70°-80°   | 5.2    | 1.5       |
| 80°-90°   | 1.6    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 202.6  | 58.9      |
| 0°-40°    | 276.7  | 80.4      |
| 0°-60°    | 328.0  | 95.3      |
| 0°-90°    | 344.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 344.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 358 |      |
| 5°  | 349 | 33   |
| 15° | 285 | 79   |
| 25° | 198 | 91   |
| 35° | 120 | 74   |
| 45° | 47  | 37   |
| 55° | 14  | 14   |
| 65° | 9   | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1281516

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 358.4 |
| 1°    | 357.9 |
| 2°    | 357.1 |
| 3°    | 355.4 |
| 4°    | 352.8 |
| 5°    | 349.4 |
| 6°    | 345.2 |
| 7°    | 340.9 |
| 8°    | 335.4 |
| 9°    | 329.9 |
| 10°   | 323.5 |
| 11°   | 316.7 |
| 12°   | 309.5 |
| 13°   | 301.4 |
| 14°   | 292.9 |
| 15°   | 284.8 |
| 17.5° | 263.1 |
| 20°   | 241.0 |
| 22.5° | 218.5 |
| 25°   | 198.1 |
| 27.5° | 178.1 |
| 30°   | 158.6 |
| 32.5° | 139.0 |
| 35°   | 119.5 |
| 37.5° | 99.9  |
| 40°   | 80.8  |
| 42.5° | 62.9  |
| 45°   | 47.2  |
| 47.5° | 34.0  |
| 50°   | 23.4  |
| 52.5° | 17.0  |
| 55°   | 14.5  |
| 57.5° | 13.2  |
| 60°   | 11.9  |
| 62.5° | 10.6  |
| 65°   | 9.4   |
| 67.5° | 8.1   |
| 70°   | 7.2   |
| 72.5° | 6.0   |
| 75°   | 4.7   |
| 77.5° | 3.8   |
| 80°   | 3.0   |
| 82.5° | 2.1   |
| 85°   | 1.3   |
| 87.5° | 0.9   |



TEST NUMBER: P1281516

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLD1WH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)