

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282515

Luminaire Tested: P3AS05R70B2750DE010 E3DLP1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70B2750DE010 E3DLP1LI_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 286.1 lumens
Efficiency: N/A
Efficacy: 48.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282515

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1LI_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282515

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1LI_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77		
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	85	75	68	64	83	74	68	63	73	67	63	71	66	63	70	65	62	61		
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67078
5°	65859
10°	62101
15°	56345
20°	49284
25°	41591
30°	34056
35°	26421
40°	18893
45°	11970
50°	5970
55°	3632
60°	3158
65°	2906
70°	2565
75°	2372
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11970 cd/sqm

TEST NUMBER: P1282515

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.9	9.8
10°-20°	69.1	24.1
20°-30°	78.7	27.5
30°-40°	61.5	21.5
40°-50°	30.2	10.6
50°-60°	9.3	3.2
60°-70°	5.5	1.9
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.7	61.4
0°-40°	237.2	82.9
0°-60°	276.7	96.7
0°-90°	286.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	286.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	306	
5°	299	28
15°	248	69
25°	172	79
35°	99	62
45°	39	30
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1282515

CATALOG NUMBER: P3AS05R70B2750DE010 E3DLP1LI_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	305.9
2.5°	304.3
5°	299.2
7.5°	290.8
10°	278.9
12.5°	265.0
15°	248.2
17.5°	230.3
20°	211.2
22.5°	191.4
25°	171.9
27.5°	152.8
30°	134.5
32.5°	116.2
35°	98.7
37.5°	82.0
40°	66.0
42.5°	51.3
45°	38.6
47.5°	27.1
50°	17.5
52.5°	11.5
55°	9.5
57.5°	8.4
60°	7.2
62.5°	6.4
65°	5.6
67.5°	4.8
70°	4.0
72.5°	3.2
75°	2.8
77.5°	2.4
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)