

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281541

Luminaire Tested: P3AS05R35B2750DE010 E3DLP1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281541
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R35B2750DE010 E3DLP1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 275.9 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281541
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281541
 CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	95	95	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	87	87	87	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	81	81	81	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	76	76	76	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	71	71	71	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	66	66	66	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	62	62	62	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	59	59	59	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	56	56	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	53	53	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88721
5°	86529
10°	79112
15°	67151
20°	53158
25°	40212
30°	29270
35°	19782
40°	12166
45°	6977
50°	4196
55°	3403
60°	2982
65°	2646
70°	2180
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6977 cd/sqm



TEST NUMBER: P1281541

CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	13.2
10°-20°	81.5	29.6
20°-30°	76.3	27.6
30°-40°	46.7	16.9
40°-50°	18.4	6.7
50°-60°	8.1	2.9
60°-70°	5.0	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.2	70.4
0°-40°	240.8	87.3
0°-60°	267.3	96.9
0°-90°	275.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	405	
5°	393	36
15°	296	82
25°	166	76
35°	74	47
45°	22	18
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1281541
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	404.6
1°	405.0
2°	403.7
3°	401.2
4°	397.3
5°	393.1
6°	387.6
7°	381.2
8°	373.5
9°	365.0
10°	355.3
11°	345.1
12°	334.0
13°	322.1
14°	309.0
15°	295.8
17.5°	261.8
20°	227.8
22.5°	195.1
25°	166.2
27.5°	139.4
30°	115.6
32.5°	93.5
35°	73.9
37.5°	56.5
40°	42.5
42.5°	30.6
45°	22.5
47.5°	16.1
50°	12.3
52.5°	10.2
55°	8.9
57.5°	7.6
60°	6.8
62.5°	5.9
65°	5.1
67.5°	4.2
70°	3.4
72.5°	3.0
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4



TEST NUMBER: P1281541
CATALOG NUMBER: P3AS05R35B2750DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)