

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281581

Luminaire Tested: P3AS05R40B2750DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3CB1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.9 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281581

CATALOG NUMBER: P3AS05R40B2750DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281581

CATALOG NUMBER: P3AS05R40B2750DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85			
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82			
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79			
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76			
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73			
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314339
5°	312832
10°	302622
15°	267743
20°	174689
25°	61891
30°	13116
35°	4310
40°	1574
45°	527
50°	443
55°	497
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 672 cd/sqm

TEST NUMBER: P1281581

CATALOG NUMBER: P3AS05R40B2750DE010 E3CB1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.7	22.4
10°-20°	311.4	52.2
20°-30°	135.1	22.6
30°-40°	12.4	2.1
40°-50°	1.8	0.3
50°-60°	1.1	0.2
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	580.3	97.2
0°-40°	592.7	99.3
0°-60°	595.6	99.8
0°-90°	596.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1434	
5°	1421	134
15°	1179	311
25°	256	135
35°	16	12
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281581

CATALOG NUMBER: P3AS05R40B2750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1433.5
2.5°	1431.8
5°	1421.2
7.5°	1398.6
10°	1359.1
12.5°	1292.4
15°	1179.4
17.5°	992.1
20°	748.6
22.5°	486.0
25°	255.8
27.5°	110.0
30°	51.8
32.5°	28.0
35°	16.1
37.5°	9.8
40°	5.5
42.5°	3.0
45°	1.7
47.5°	1.3
50°	1.3
52.5°	1.3
55°	1.3
57.5°	1.3
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)