

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281600

Luminaire Tested: P3AS05R40B2750DE010 E3D1H_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3D1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 557.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281600

CATALOG NUMBER: P3AS05R40B2750DE010 E3D1H_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281600

CATALOG NUMBER: P3AS05R40B2750DE010 E3D1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96											
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92											
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88											
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85											
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82											
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79											
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76											
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73											
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70											
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283925
5°	281861
10°	274499
15°	245200
20°	162577
25°	60899
30°	16281
35°	6371
40°	2290
45°	1085
50°	341
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1085 cd/sqm

TEST NUMBER: P1281600

CATALOG NUMBER: P3AS05R40B2750DE010 E3D1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	21.7
10°-20°	286.2	51.4
20°-30°	129.8	23.3
30°-40°	16.8	3.0
40°-50°	2.9	0.5
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.8	96.4
0°-40°	553.6	99.4
0°-60°	556.9	100.0
0°-90°	557.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	557.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1295	
5°	1280	121
15°	1080	286
25°	252	130
35°	24	17
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1281600

CATALOG NUMBER: P3AS05R40B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1294.8
1°	1294.0
2°	1292.0
3°	1289.1
4°	1285.4
5°	1280.5
6°	1274.9
7°	1267.9
8°	1259.3
9°	1247.6
10°	1232.8
11°	1215.4
12°	1192.2
13°	1163.5
14°	1126.1
15°	1080.1
16°	1021.4
17°	954.5
18°	874.2
19°	789.3
20°	696.7
21°	604.1
22°	512.8
23°	422.0
24°	332.7
25°	251.7
26°	186.4
27°	136.5
28°	102.6
29°	79.8
30°	64.3
31°	53.2
32°	44.5
32.5°	40.6
33°	36.7
34°	29.8
35°	23.8
36°	18.7
37°	14.8
37.5°	13.3
38°	11.7
39°	9.7
40°	8.0
42.5°	5.3
45°	3.5



TEST NUMBER: P1281600

CATALOG NUMBER: P3AS05R40B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.1
50°	1.0
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)