

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281616

Luminaire Tested: P3AS05R40B2750DE010 E3D1WH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3D1WH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281616
CATALOG NUMBER: P3AS05R40B2750DE010 E3D1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281616
 CATALOG NUMBER: P3AS05R40B2750DE010 E3D1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92	92	92	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88	88	88	88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85	85	85	85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82	82	82	82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79	79	79	79
7	93	86	81	78	92	85	81	78	84	80	78	83	80	77	82	79	77	76	76	76	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73	73	73	73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70	70	70	70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68	68	68	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	303287
5°	301100
10°	293225
15°	261931
20°	173662
25°	65060
30°	17395
35°	6799
40°	2433
45°	1147
50°	341
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1147 cd/sqm



TEST NUMBER: P1281616
 CATALOG NUMBER: P3AS05R40B2750DE010 E3D1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	21.7
10°-20°	305.7	51.4
20°-30°	138.6	23.3
30°-40°	18.0	3.0
40°-50°	3.1	0.5
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	573.4	96.4
0°-40°	591.4	99.4
0°-60°	594.8	100.0
0°-90°	595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1383	
5°	1368	129
15°	1154	306
25°	269	139
35°	25	18
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1281616
CATALOG NUMBER: P3AS05R40B2750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1383.1
1°	1382.3
2°	1380.2
3°	1377.1
4°	1373.1
5°	1367.9
6°	1361.8
7°	1354.3
8°	1345.2
9°	1332.7
10°	1316.9
11°	1298.3
12°	1273.5
13°	1242.9
14°	1202.9
15°	1153.8
16°	1091.1
17°	1019.6
18°	933.8
19°	843.2
20°	744.2
21°	645.3
22°	547.8
23°	450.8
24°	355.4
25°	268.9
26°	199.1
27°	145.8
28°	109.6
29°	85.2
30°	68.7
31°	56.9
32°	47.5
32.5°	43.3
33°	39.2
34°	31.9
35°	25.4
36°	20.0
37°	15.8
37.5°	14.2
38°	12.5
39°	10.4
40°	8.5
42.5°	5.6
45°	3.7



TEST NUMBER: P1281616
CATALOG NUMBER: P3AS05R40B2750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.3
50°	1.0
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)