

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282655

Luminaire Tested: P3AS09R15B2750DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15B2750DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 463.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282655

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282655

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	109	106	104		110	107	105	102		103	101	99		99	98	96		96	95	93		91			
2	106	100	96	92		104	99	95	91		95	92	89		92	90	87		90	87	85		83			
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78		76			
4	94	86	80	75		92	85	79	74		82	77	73		80	76	73		78	75	72		70			
5	89	80	73	68		87	79	73	68		77	72	67		75	70	67		74	69	66		65			
6	84	74	68	63		83	73	67	63		72	66	62		70	66	62		69	65	61		60			
7	80	69	63	58		78	69	63	58		67	62	58		66	61	57		65	61	57		56			
8	76	65	59	54		74	65	58	54		63	58	54		62	57	54		61	57	53		52			
9	72	61	55	51		71	61	55	51		60	54	50		59	54	50		58	53	50		49			
10	68	58	52	48		67	57	51	47		57	51	47		56	51	47		55	50	47		46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116789
5°	113625
10°	103828
15°	90943
20°	78010
25°	65133
30°	52135
35°	39110
40°	28367
45°	18545
50°	11599
55°	7837
60°	6929
65°	6382
70°	6027
75°	5507
80°	5177
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18545 cd/sqm

TEST NUMBER: P1282655

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.6	10.3
10°-20°	111.6	24.1
20°-30°	123.0	26.6
30°-40°	92.1	19.9
40°-50°	47.7	10.3
50°-60°	19.8	4.3
60°-70°	12.3	2.6
70°-80°	6.9	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.2	61.0
0°-40°	374.3	80.8
0°-60°	441.9	95.4
0°-90°	463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	463.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	533	
5°	516	48
15°	401	112
25°	269	123
35°	146	92
45°	60	48
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1282655

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	532.6
1°	533.2
2°	531.4
3°	527.9
4°	522.6
5°	516.2
6°	508.0
7°	499.2
8°	488.6
9°	477.4
10°	466.3
12.5°	434.0
15°	400.6
17.5°	367.2
20°	334.3
22.5°	300.9
25°	269.2
27.5°	237.6
30°	205.9
32.5°	174.8
35°	146.1
37.5°	121.4
40°	99.1
42.5°	78.6
45°	59.8
47.5°	45.2
50°	34.0
52.5°	25.2
55°	20.5
57.5°	18.2
60°	15.8
62.5°	14.1
65°	12.3
67.5°	10.6
70°	9.4
72.5°	7.6
75°	6.5
77.5°	5.3
80°	4.1
82.5°	2.9
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)