

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281626

Luminaire Tested: P3AS05R40B2750DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3DL1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 243.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281626

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281626

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96		94
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91		89
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90	88	86		84
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81		80
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83	80	77		76
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79	76	73		72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76	73	70		69
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73	69	67		65
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70	66	64		63
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67	64	61		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107535
5°	104402
10°	94743
15°	78275
20°	56448
25°	34913
30°	18914
35°	9771
40°	5324
45°	2977
50°	1501
55°	1109
60°	1009
65°	986
70°	962
75°	847
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2977 cd/sqm

TEST NUMBER: P1281626

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.7	18.0
10°-20°	93.9	38.6
20°-30°	67.0	27.6
30°-40°	24.7	10.2
40°-50°	7.8	3.2
50°-60°	2.7	1.1
60°-70°	1.9	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.6	84.2
0°-40°	229.3	94.3
0°-60°	239.7	98.7
0°-90°	243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	243.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	474	44
15°	345	94
25°	144	67
35°	36	25
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281626

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	490.4
2.5°	486.6
5°	474.3
7.5°	453.9
10°	425.5
12.5°	389.4
15°	344.8
17.5°	294.7
20°	241.9
22.5°	190.0
25°	144.3
27.5°	106.0
30°	74.7
32.5°	52.4
35°	36.5
37.5°	25.9
40°	18.6
42.5°	13.3
45°	9.6
47.5°	6.5
50°	4.4
52.5°	3.1
55°	2.9
57.5°	2.7
60°	2.3
62.5°	2.1
65°	1.9
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)