

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281650

Luminaire Tested: P3AS05R40B2750DE010 E3DL1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3DL1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 464.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281650

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281650

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	92	91
3	104	99	94	91		102	97	93	90		95	91	88		92	89	87		90	88	86
4	100	93	88	85		98	92	88	84		90	86	83		88	85	82		86	84	81
5	96	88	83	79		94	88	83	79		86	82	78		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	77	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	68		84	76	71	67		75	70	67		74	70	67		73	69	67
9	82	73	68	64		81	73	68	64		72	67	64		71	67	64		70	66	64
10	78	70	65	62		78	70	65	61		69	64	61		68	64	61		67	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205312
5°	199361
10°	180914
15°	149445
20°	107809
25°	66681
30°	36107
35°	18658
40°	10133
45°	5675
50°	2866
55°	2141
60°	1930
65°	1868
70°	1795
75°	1694
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5675 cd/sqm

TEST NUMBER: P1281650

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	18.0
10°-20°	179.3	38.6
20°-30°	127.9	27.6
30°-40°	47.1	10.2
40°-50°	14.8	3.2
50°-60°	5.2	1.1
60°-70°	3.6	0.8
70°-80°	2.1	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.7	84.2
0°-40°	437.8	94.3
0°-60°	457.8	98.6
0°-90°	464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	464.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	936	
5°	906	83
15°	658	179
25°	276	128
35°	70	47
45°	18	15
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1281650

CATALOG NUMBER: P3AS05R40B2750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	936.3
2.5°	929.2
5°	905.7
7.5°	866.6
10°	812.5
12.5°	743.6
15°	658.3
17.5°	562.7
20°	462.0
22.5°	362.8
25°	275.6
27.5°	202.3
30°	142.6
32.5°	100.0
35°	69.7
37.5°	49.4
40°	35.4
42.5°	25.5
45°	18.3
47.5°	12.3
50°	8.4
52.5°	6.0
55°	5.6
57.5°	5.2
60°	4.4
62.5°	4.0
65°	3.6
67.5°	3.2
70°	2.8
72.5°	2.4
75°	2.0
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)