

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281652

Luminaire Tested: P3AS05R40B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 174.0 lumens
Efficiency: N/A
Efficacy: 29.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281652
CATALOG NUMBER: P3AS05R40B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1281652
 CATALOG NUMBER: P3AS05R40B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39054
5°	38345
10°	36161
15°	32827
20°	28843
25°	24630
30°	20408
35°	15740
40°	11192
45°	7536
50°	4128
55°	2906
60°	2719
65°	2542
70°	2244
75°	2118
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7536 cd/sqm



TEST NUMBER: P1281652
 CATALOG NUMBER: P3AS05R40B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	9.3
10°-20°	40.3	23.2
20°-30°	46.6	26.8
30°-40°	36.7	21.1
40°-50°	18.8	10.8
50°-60°	7.2	4.1
60°-70°	4.8	2.7
70°-80°	2.6	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.1	59.3
0°-40°	139.8	80.4
0°-60°	165.9	95.3
0°-90°	174.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	174.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	178	
5°	174	16
15°	145	40
25°	102	47
35°	59	37
45°	24	19
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1281652
CATALOG NUMBER: P3AS05R40B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	178.1
2.5°	177.2
5°	174.2
7.5°	169.2
10°	162.4
12.5°	154.4
15°	144.6
17.5°	134.5
20°	123.6
22.5°	112.5
25°	101.8
27.5°	91.1
30°	80.6
32.5°	69.9
35°	58.8
37.5°	48.5
40°	39.1
42.5°	31.1
45°	24.3
47.5°	17.7
50°	12.1
52.5°	8.8
55°	7.6
57.5°	6.8
60°	6.2
62.5°	5.5
65°	4.9
67.5°	4.1
70°	3.5
72.5°	2.9
75°	2.5
77.5°	1.9
80°	1.4
82.5°	1.2
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)