

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282708

Luminaire Tested: P3AS09R20B2750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20B2750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 728.1 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282708

CATALOG NUMBER: P3AS09R20B2750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282708

CATALOG NUMBER: P3AS09R20B2750DE010 E3CB1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98			98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	95			95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	93			93
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	91			91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90			90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	92	90	89	88			88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86			86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85			85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83			83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	82			82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1130677
5°	981375
10°	606379
15°	210626
20°	64686
25°	22864
30°	8457
35°	3400
40°	1803
45°	713
50°	409
55°	459
60°	526
65°	311
70°	385
75°	508
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1282708

CATALOG NUMBER: P3AS09R20B2750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	370.0	50.8
10°-20°	293.6	40.3
20°-30°	50.8	7.0
30°-40°	9.2	1.3
40°-50°	2.1	0.3
50°-60°	1.1	0.1
60°-70°	0.7	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.4	98.1
0°-40°	723.7	99.4
0°-60°	726.9	99.8
0°-90°	728.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5156	
5°	4458	370
15°	928	294
25°	94	51
35°	13	9
45°	2	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282708

CATALOG NUMBER: P3AS09R20B2750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5156.3
1°	5131.5
2°	5033.5
3°	4876.2
4°	4691.8
5°	4458.4
6°	4191.0
7°	3879.9
8°	3525.5
9°	3127.3
10°	2723.3
12.5°	1717.8
15°	927.8
17.5°	495.6
20°	277.2
22.5°	158.5
25°	94.5
27.5°	57.6
30°	33.4
32.5°	19.6
35°	12.7
37.5°	8.6
40°	6.3
42.5°	4.0
45°	2.3
47.5°	1.2
50°	1.2
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)