

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281771

Luminaire Tested: P3AS05R45B2750DE010 E3DL1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45B2750DE010 E3DL1WH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 307.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281771

CATALOG NUMBER: P3AS05R45B2750DE010 E3DL1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281771

CATALOG NUMBER: P3AS05R45B2750DE010 E3DL1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91440
5°	89368
10°	82430
15°	71669
20°	58875
25°	45825
30°	33828
35°	23798
40°	14856
45°	8063
50°	4367
55°	3747
60°	3377
65°	2854
70°	2436
75°	2542
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8063 cd/sqm

TEST NUMBER: P1281771

CATALOG NUMBER: P3AS05R45B2750DE010 E3DL1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	12.2
10°-20°	87.3	28.4
20°-30°	86.7	28.2
30°-40°	55.8	18.2
40°-50°	21.5	7.0
50°-60°	8.7	2.8
60°-70°	5.5	1.8
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.5	68.9
0°-40°	267.3	87.1
0°-60°	297.6	96.9
0°-90°	307.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	307.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	417	
5°	406	38
15°	316	87
25°	189	87
35°	89	56
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1281771

CATALOG NUMBER: P3AS05R45B2750DE010 E3DL1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	417.0
2.5°	414.9
5°	406.0
7.5°	390.6
10°	370.2
12.5°	344.7
15°	315.7
17.5°	284.3
20°	252.3
22.5°	220.0
25°	189.4
27.5°	160.4
30°	133.6
32.5°	110.2
35°	88.9
37.5°	69.8
40°	51.9
42.5°	37.4
45°	26.0
47.5°	17.4
50°	12.8
52.5°	10.6
55°	9.8
57.5°	8.5
60°	7.7
62.5°	6.4
65°	5.5
67.5°	4.7
70°	3.8
72.5°	3.4
75°	3.0
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)