

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282726

Luminaire Tested: P3AS09R20B2750DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20B2750DE010 E3CD1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 80CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282726
CATALOG NUMBER: P3AS09R20B2750DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282726
 CATALOG NUMBER: P3AS09R20B2750DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99		98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97		95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95		93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92		91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91		90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89		88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87		86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85		85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84		83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1228520
5°	1066297
10°	658861
15°	228832
20°	70286
25°	24848
30°	9191
35°	3694
40°	1975
45°	775
50°	443
55°	497
60°	570
65°	311
70°	385
75°	508
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 775 cd/sqm



TEST NUMBER: P1282726
 CATALOG NUMBER: P3AS09R20B2750DE010 E3CD1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.0	50.8
10°-20°	319.0	40.3
20°-30°	55.2	7.0
30°-40°	10.0	1.3
40°-50°	2.3	0.3
50°-60°	1.2	0.1
60°-70°	0.7	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.3	98.1
0°-40°	786.3	99.4
0°-60°	789.8	99.8
0°-90°	791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5602	
5°	4844	402
15°	1008	319
25°	103	55
35°	14	10
45°	2	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1282726
CATALOG NUMBER: P3AS09R20B2750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5602.5
1°	5575.5
2°	5469.1
3°	5298.2
4°	5097.8
5°	4844.2
6°	4553.7
7°	4215.6
8°	3830.6
9°	3397.9
10°	2959.0
12.5°	1866.4
15°	1008.0
17.5°	538.5
20°	301.2
22.5°	172.2
25°	102.7
27.5°	62.6
30°	36.3
32.5°	21.3
35°	13.8
37.5°	9.4
40°	6.9
42.5°	4.4
45°	2.5
47.5°	1.3
50°	1.3
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)