

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282757

Luminaire Tested: P3AS09R20B2750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20B2750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282757

CATALOG NUMBER: P3AS09R20B2750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1282757

CATALOG NUMBER: P3AS09R20B2750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228512
5°	207726
10°	153526
15°	94961
20°	54231
25°	30970
30°	17370
35°	9450
40°	5181
45°	2853
50°	1672
55°	1223
60°	1140
65°	1038
70°	898
75°	932
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2853 cd/sqm

TEST NUMBER: P1282757

CATALOG NUMBER: P3AS09R20B2750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	27.5
10°-20°	116.7	39.3
20°-30°	60.9	20.5
30°-40°	23.5	7.9
40°-50°	7.6	2.6
50°-60°	3.0	1.0
60°-70°	2.0	0.7
70°-80°	1.2	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	259.3	87.3
0°-40°	282.8	95.2
0°-60°	293.5	98.8
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	944	82
15°	418	117
25°	128	61
35°	35	24
45°	9	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282757

CATALOG NUMBER: P3AS09R20B2750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1042.1
1°	1040.1
2°	1027.7
3°	1008.8
4°	979.5
5°	943.7
6°	901.2
7°	854.1
8°	799.6
9°	746.6
10°	689.5
12.5°	548.0
15°	418.3
17.5°	313.0
20°	232.4
22.5°	172.1
25°	128.0
27.5°	94.4
30°	68.6
32.5°	49.6
35°	35.3
37.5°	25.5
40°	18.1
42.5°	12.9
45°	9.2
47.5°	6.6
50°	4.9
52.5°	3.7
55°	3.2
57.5°	2.9
60°	2.6
62.5°	2.3
65°	2.0
67.5°	1.7
70°	1.4
72.5°	1.4
75°	1.1
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)