

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281780

Luminaire Tested: P3AS05R45B2750DE010 E3DLD1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45B2750DE010 E3DLD1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281780

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281780

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35830
5°	35197
10°	33310
15°	30375
20°	26859
25°	23324
30°	20028
35°	16677
40°	12423
45°	7598
50°	3514
55°	2753
60°	2631
65°	2439
70°	2244
75°	2118
80°	2020
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7598 cd/sqm

TEST NUMBER: P1281780

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.9	8.8
10°-20°	37.3	22.0
20°-30°	44.3	26.2
30°-40°	38.5	22.8
40°-50°	19.3	11.4
50°-60°	6.7	4.0
60°-70°	4.7	2.8
70°-80°	2.6	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.5	57.1
0°-40°	134.9	79.8
0°-60°	160.9	95.2
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	163	
5°	160	15
15°	134	37
25°	96	44
35°	62	38
45°	24	19
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1281780

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLD1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	163.4
2.5°	162.6
5°	159.9
7.5°	155.6
10°	149.6
12.5°	142.2
15°	133.8
17.5°	124.5
20°	115.1
22.5°	105.6
25°	96.4
27.5°	87.6
30°	79.1
32.5°	70.9
35°	62.3
37.5°	53.2
40°	43.4
42.5°	33.9
45°	24.5
47.5°	16.2
50°	10.3
52.5°	8.0
55°	7.2
57.5°	6.6
60°	6.0
62.5°	5.5
65°	4.7
67.5°	4.1
70°	3.5
72.5°	2.9
75°	2.5
77.5°	1.9
80°	1.6
82.5°	1.2
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)