

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282811

Luminaire Tested: P3AS09R20B2750DE010 E3DLD1WMH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1282811  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R20B2750DE010 E3DLD1WMH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 493.0 lumens  
Efficiency: N/A  
Efficacy: 37.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1282811

CATALOG NUMBER: P3AS09R20B2750DE010 E3DLD1WMH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1282811

CATALOG NUMBER: P3AS09R20B2750DE010 E3DLD1WMH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 90  |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 53  |  | 61  |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 121942 |
| 5°  | 118688 |
| 10° | 109194 |
| 15° | 96096  |
| 20° | 82420  |
| 25° | 69246  |
| 30° | 55983  |
| 35° | 42590  |
| 40° | 30285  |
| 45° | 20002  |
| 50° | 12383  |
| 55° | 8143   |
| 60° | 7412   |
| 65° | 6849   |
| 70° | 6411   |
| 75° | 5846   |
| 80° | 5556   |
| 85° | 4780   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20002 cd/sqm

TEST NUMBER: P1282811

CATALOG NUMBER: P3AS09R20B2750DE010 E3DLD1WMH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 49.9   | 10.1      |
| 10°-20°   | 117.9  | 23.9      |
| 20°-30°   | 130.8  | 26.5      |
| 30°-40°   | 99.8   | 20.2      |
| 40°-50°   | 51.1   | 10.4      |
| 50°-60°   | 21.0   | 4.3       |
| 60°-70°   | 13.1   | 2.7       |
| 70°-80°   | 7.3    | 1.5       |
| 80°-90°   | 2.1    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 298.6  | 60.6      |
| 0°-40°    | 398.4  | 80.8      |
| 0°-60°    | 470.4  | 95.4      |
| 0°-90°    | 493.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 493.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 556 |      |
| 5°  | 539 | 50   |
| 15° | 423 | 118  |
| 25° | 286 | 131  |
| 35° | 159 | 100  |
| 45° | 64  | 51   |
| 55° | 21  | 21   |
| 65° | 13  | 13   |
| 75° | 7   | 7    |
| 85° | 2   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1282811

CATALOG NUMBER: P3AS09R20B2750DE010 E3DLD1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 556.1 |
| 1°    | 556.7 |
| 2°    | 554.2 |
| 3°    | 551.1 |
| 4°    | 546.1 |
| 5°    | 539.2 |
| 6°    | 531.1 |
| 7°    | 522.3 |
| 8°    | 512.9 |
| 9°    | 501.6 |
| 10°   | 490.4 |
| 12.5° | 457.8 |
| 15°   | 423.3 |
| 17.5° | 388.3 |
| 20°   | 353.2 |
| 22.5° | 318.1 |
| 25°   | 286.2 |
| 27.5° | 254.3 |
| 30°   | 221.1 |
| 32.5° | 189.8 |
| 35°   | 159.1 |
| 37.5° | 132.1 |
| 40°   | 105.8 |
| 42.5° | 83.3  |
| 45°   | 64.5  |
| 47.5° | 48.8  |
| 50°   | 36.3  |
| 52.5° | 26.9  |
| 55°   | 21.3  |
| 57.5° | 19.4  |
| 60°   | 16.9  |
| 62.5° | 15.0  |
| 65°   | 13.2  |
| 67.5° | 11.3  |
| 70°   | 10.0  |
| 72.5° | 8.1   |
| 75°   | 6.9   |
| 77.5° | 5.6   |
| 80°   | 4.4   |
| 82.5° | 3.1   |
| 85°   | 1.9   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)