

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281826

Luminaire Tested: P3AS05R45B2750DE010 E3DLP1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45B2750DE010 E3DLP1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 307.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281826

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281826

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	96	94		93			
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87		86			
3	102	95	90	85		100	93	89	85		91	87	83		88	85	82		86	83	81		79			
4	96	88	83	78		94	87	82	78		85	81	77		83	79	76		81	78	75		74			
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70		69			
6	87	78	72	67		85	77	71	67		75	70	66		74	69	66		73	69	66		64			
7	83	73	67	63		81	72	67	63		71	66	62		70	65	62		69	65	61		60			
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58		56			
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55		53			
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52		50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91440
5°	89368
10°	82430
15°	71669
20°	58875
25°	45825
30°	33828
35°	23798
40°	14856
45°	8063
50°	4367
55°	3747
60°	3377
65°	2854
70°	2436
75°	2542
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8063 cd/sqm

TEST NUMBER: P1281826

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	12.2
10°-20°	87.3	28.4
20°-30°	86.7	28.2
30°-40°	55.8	18.2
40°-50°	21.5	7.0
50°-60°	8.7	2.8
60°-70°	5.5	1.8
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.5	68.9
0°-40°	267.3	87.1
0°-60°	297.6	96.9
0°-90°	307.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	307.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	417	
5°	406	38
15°	316	87
25°	189	87
35°	89	56
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1281826

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	417.0
2.5°	414.9
5°	406.0
7.5°	390.6
10°	370.2
12.5°	344.7
15°	315.7
17.5°	284.3
20°	252.3
22.5°	220.0
25°	189.4
27.5°	160.4
30°	133.6
32.5°	110.2
35°	88.9
37.5°	69.8
40°	51.9
42.5°	37.4
45°	26.0
47.5°	17.4
50°	12.8
52.5°	10.6
55°	9.8
57.5°	8.5
60°	7.7
62.5°	6.4
65°	5.5
67.5°	4.7
70°	3.8
72.5°	3.4
75°	3.0
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)