

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281830

Luminaire Tested: P3AS05R45B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 445.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281830

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1281830

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96		94			
2	109	104	100	97		106	102	99	96		99	96	94		96	94	92		93	91	90		88			
3	104	98	93	89		102	96	92	88		94	90	87		91	88	86		89	86	84		83			
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79		78			
5	94	87	81	77		93	86	81	77		84	80	76		82	79	76		81	78	75		74			
6	90	82	76	73		89	81	76	72		80	75	72		78	74	71		77	74	71		69			
7	86	78	72	68		85	77	72	68		76	71	68		75	71	67		74	70	67		66			
8	83	74	68	65		82	73	68	64		72	68	64		71	67	64		70	67	64		62			
9	79	70	65	61		78	70	65	61		69	64	61		68	64	61		67	63	61		59			
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58		57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167114
5°	163196
10°	150008
15°	127106
20°	98615
25°	68931
30°	43424
35°	25565
40°	14456
45°	7039
50°	2456
55°	1988
60°	1930
65°	1868
70°	1795
75°	1694
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7039 cd/sqm

TEST NUMBER: P1281830

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	15.4
10°-20°	153.8	34.6
20°-30°	130.6	29.3
30°-40°	62.3	14.0
40°-50°	18.8	4.2
50°-60°	4.8	1.1
60°-70°	3.6	0.8
70°-80°	2.1	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.0	79.3
0°-40°	415.2	93.3
0°-60°	438.7	98.6
0°-90°	445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	762	
5°	741	69
15°	560	154
25°	285	131
35°	96	62
45°	23	19
55°	5	5
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1281830

CATALOG NUMBER: P3AS05R45B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	762.1
2.5°	757.3
5°	741.4
7.5°	713.9
10°	673.7
12.5°	620.4
15°	559.9
17.5°	492.7
20°	422.6
22.5°	351.4
25°	284.9
27.5°	224.5
30°	171.5
32.5°	128.9
35°	95.5
37.5°	70.4
40°	50.5
42.5°	35.0
45°	22.7
47.5°	12.7
50°	7.2
52.5°	5.6
55°	5.2
57.5°	4.8
60°	4.4
62.5°	4.0
65°	3.6
67.5°	3.2
70°	2.8
72.5°	2.4
75°	2.0
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)