

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1281858

Luminaire Tested: P3AS05R50B2750DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1281858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R50B2750DE010 E3CD1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 536.1 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1281858

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1281858

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	101	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87	84	82	80
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83	80	77	76
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76	72	70	69
8	85	76	71	67	83	76	71	67	75	70	67		74	70	67		73	69	66	65
9	81	73	68	64	80	72	67	64	71	67	64		71	66	63		70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	61		68	63	61		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186674
5°	183337
10°	176038
15°	161408
20°	142346
25°	109095
30°	59326
35°	19086
40°	4494
45°	620
50°	546
55°	612
60°	526
65°	623
70°	513
75°	678
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 1006 cd/sqm

TEST NUMBER: P1281858

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	14.6
10°-20°	197.6	36.9
20°-30°	197.9	36.9
30°-40°	55.7	10.4
40°-50°	3.4	0.6
50°-60°	1.3	0.2
60°-70°	1.0	0.2
70°-80°	0.7	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.8	88.4
0°-40°	529.4	98.8
0°-60°	534.1	99.6
0°-90°	536.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	536.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	851	
5°	833	78
15°	711	198
25°	451	198
35°	71	56
45°	2	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1281858

CATALOG NUMBER: P3AS05R50B2750DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	851.3
2.5°	847.0
5°	832.9
7.5°	813.7
10°	790.6
12.5°	755.7
15°	711.0
17.5°	659.7
20°	610.0
22.5°	548.1
25°	450.9
27.5°	335.7
30°	234.3
32.5°	141.4
35°	71.3
37.5°	33.7
40°	15.7
42.5°	5.9
45°	2.0
47.5°	1.6
50°	1.6
52.5°	1.6
55°	1.6
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)