

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282833

Luminaire Tested: P3AS09R25B2750DE010 E3CB1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3CB1MB_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 734.1 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282833

CATALOG NUMBER: P3AS09R25B2750DE010 E3CB1MB_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282833

CATALOG NUMBER: P3AS09R25B2750DE010 E3CB1MB_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	784762
5°	727843
10°	564452
15°	283021
20°	92991
25°	36970
30°	13876
35°	4015
40°	1803
45°	713
50°	580
55°	459
60°	526
65°	623
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 758 cd/sqm

TEST NUMBER: P1282833

CATALOG NUMBER: P3AS09R25B2750DE010 E3CB1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.8	39.6
10°-20°	347.0	47.3
20°-30°	78.2	10.7
30°-40°	12.7	1.7
40°-50°	2.3	0.3
50°-60°	1.2	0.2
60°-70°	1.1	0.2
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.0	97.5
0°-40°	728.7	99.3
0°-60°	732.2	99.8
0°-90°	734.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3579	
5°	3307	291
15°	1247	347
25°	153	78
35°	15	13
45°	2	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282833

CATALOG NUMBER: P3AS09R25B2750DE010 E3CB1MB_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3578.8
1°	3573.0
2°	3544.2
3°	3491.1
4°	3410.9
5°	3306.6
6°	3182.0
7°	3047.1
8°	2892.5
9°	2723.6
10°	2535.0
11°	2317.6
12°	2067.3
13°	1805.5
14°	1524.7
15°	1246.7
17.5°	710.4
20°	398.5
22.5°	240.5
25°	152.8
27.5°	94.0
30°	54.8
32.5°	28.8
35°	15.0
37.5°	9.8
40°	6.3
42.5°	4.0
45°	2.3
47.5°	1.7
50°	1.7
52.5°	1.7
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1282833

CATALOG NUMBER: P3AS09R25B2750DE010 E3CB1MB_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)