

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282856

Luminaire Tested: P3AS09R25B2750DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3CD1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 797.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282856

CATALOG NUMBER: P3AS09R25B2750DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282856

CATALOG NUMBER: P3AS09R25B2750DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	852103
5°	790313
10°	612903
15°	307312
20°	100972
25°	40139
30°	15066
35°	4363
40°	1975
45°	775
50°	648
55°	497
60°	570
65°	675
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 775 cd/sqm

TEST NUMBER: P1282856

CATALOG NUMBER: P3AS09R25B2750DE010 E3CD1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.8	39.6
10°-20°	376.8	47.3
20°-30°	84.9	10.7
30°-40°	13.8	1.7
40°-50°	2.5	0.3
50°-60°	1.4	0.2
60°-70°	1.2	0.2
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.5	97.5
0°-40°	791.3	99.3
0°-60°	795.1	99.8
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3886	
5°	3590	316
15°	1354	377
25°	166	85
35°	16	14
45°	2	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1282856

CATALOG NUMBER: P3AS09R25B2750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3885.9
1°	3879.7
2°	3848.4
3°	3790.8
4°	3703.7
5°	3590.4
6°	3455.1
7°	3308.6
8°	3140.8
9°	2957.3
10°	2752.6
11°	2516.5
12°	2244.8
13°	1960.5
14°	1655.6
15°	1353.7
17.5°	771.4
20°	432.7
22.5°	261.1
25°	165.9
27.5°	102.1
30°	59.5
32.5°	31.3
35°	16.3
37.5°	10.6
40°	6.9
42.5°	4.4
45°	2.5
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1282856

CATALOG NUMBER: P3AS09R25B2750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)