

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282885

Luminaire Tested: P3AS09R25B2750DE010 E3D1WMH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25B2750DE010 E3D1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 793.1 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282885

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1282885

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	868483
5°	804532
10°	622478
15°	297323
20°	98032
25°	41325
30°	16028
35°	6933
40°	2319
45°	1085
50°	409
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1085 cd/sqm

TEST NUMBER: P1282885

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.3	40.5
10°-20°	365.4	46.1
20°-30°	84.9	10.7
30°-40°	17.8	2.2
40°-50°	2.9	0.4
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	771.6	97.3
0°-40°	789.4	99.5
0°-60°	792.8	100.0
0°-90°	793.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3961	
5°	3655	321
15°	1310	365
25°	171	85
35°	26	18
45°	4	3
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1282885

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3960.6
1°	3952.5
2°	3911.4
3°	3853.6
4°	3765.4
5°	3655.0
6°	3513.2
7°	3364.9
8°	3198.4
9°	3010.6
10°	2795.6
11°	2546.3
12°	2260.2
13°	1946.8
14°	1619.0
15°	1309.7
16°	1035.9
17°	807.1
18°	634.8
19°	507.8
20°	420.1
21°	351.1
22°	294.7
23°	246.1
24°	205.9
25°	170.8
27.5°	101.2
30°	63.3
32.5°	40.5
35°	25.9
37.5°	15.5
40°	8.1
42.5°	5.2
45°	3.5
47.5°	2.0
50°	1.2
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1282885

CATALOG NUMBER: P3AS09R25B2750DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)